

FIXTURES & COMPONENTS

Filtrific® fixtures and components transform the application of the Filter Tank from one type of system to another. A variety of interchangeable components allow specific fine-tuning of the system at any time. Offering everything from a low profile waterfall starter to multiple skimming options, these components help bring out the best in any water feature installation, from natural waterfalls and ponds to formal concrete fountains.




FILTER BASKETS | FIXTURES & COMPONENTS

Surgical-grade stainless steel Filter Baskets separate debris from the water carried in through the skimmer. Interchangeable screen sizes provide customized filtering, to assure trouble free operation of pumps and related equipment. Finer mesh screens require more frequent cleaning than large mesh screens and are generally used with smaller pumping flows. Larger mesh screens are typically used with large flow installations.



FOUR FILTER SCREEN SIZES AVAILABLE:



FIXTURES & COMPONENTS | FILTER BASKETS



EASY-TO-REMOVE FILTERS Filtrific® Filter Tanks utilize a two piece lid, which makes the filters easily accessible; simply open the filter access cap and lift out the basket.



QUICK-CLEANING



Clean filters are essential in maintaining an efficient water feature. Routine maintenance is accomplished by occasionally emptying the Filter Baskets. If a large amount of debris has collected in the Filter Basket, simply remove the filter element and the compacted debris will fall out.



T40F FILTER BASKET

- 1 basket per T40F Filter Tank
- Provides 1.7 square feet of surface area

MODEL: E24-40

MODEL: E20-40

MODEL: E10-40

MODEL: E6-40

See pg. 11 for replacement screens



T75F FILTER BASKET

- 2 baskets per T75F Filter Tank
- Provides 1.7 square feet of surface area

MODEL: E24-75

MODEL: E20-75

MODEL: E10-75

MODEL: E6-75

See pg. 13 for replacement screens



T390F FILTER BASKET

- · 2 baskets per T390F Filter Tank
- Provides 3.4 square feet of surface area

MODEL: E20-390

MODEL: E10-390

MODEL: E6-390

See pg. 15 for replacement screens